


## Surface-mounted gong



Specification	Order No.	Packing unit	PS	EAN
 <p>pure white glossy</p>	1200 03	1	18	4010337200031

## Features

- The surface-mounted gong in the Gira door communication system is for additional signalling.
- Fully pre-assembled surface-mounted gong, which allows quick and clean mounting.
- Design diversity thanks to integration, allowing uniform appearance of door communication and electrical installation.
- Installation possible with or without frame.
- Easy installation using pull-off screw terminals.
- Easy disassembly of device during renovation work.
- Mounting holes for installation.
- Signal transmission and power supply of the surface-mounted gong via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- Parallel connection of up to three gongs or home stations possible.
- One-man start-up with easy start-up procedure.
- Operating buttons with integrated LEDs for status display.
- LED display for an incoming call.
- Ringtone deactivation is possible.
- Ringtone differentiation for door call, internal call and floor call.
- Selection of ringtone melody – up to five different ringing tone melodies can be selected.

The operating buttons of the gong control the following functions

- Setting the ringtone melody.
- Switching the ringtone on and off.
- Adjustment of ringtone volume.

## Technical data

Power supply:	via the 2-wire bus
Connections	
- 2-wire bus:	2x screw terminals
- Floor-call button:	2x screw terminals
Ambient temperature:	-5 °C to +50 °C

## Notes

- A frame is required for installation in a device box.
- A 2-gang frame without crossbar is required for installation with a frame.

---

## Dimensions in mm

Device:	W 55	H 127	D 20
---------	------	-------	------

---