




Surface-mounted video home station 7



Specification	Order No.	Packing unit	PS	EAN
 pure white glossy	1209 03	1	10	4010337053422
 black matt	1209 005	1	10	4010337053408

Features

- Fully pre-assembled unit including a 17.78 cm (7") TFT colour display and convenient speakerphone function.
- Full-surface glass front with touch functionality.
- Direct wall mounting or wall mounting with flush-mounted device box or cavity wall box.
- Mounting with base foot for placement on items of furniture.

Technical data

Power supply: DC 26 V \pm 2 V (by 2-wire bus)

Connections

- 2-wire bus: 2 x plug terminal
- Additional power supply: 2 x plug terminal
- Floor-call button: 2 x plug terminal

Display

- Diagonal: 17.78 cm (= 7")
- Colour system: PAL
- Resolution: 1024 x 600 pixels

microSD card

- Type: SDHC
- SDHC memory capacity: 32 GB
- File system: FAT 32

Ambient temperature: -5 °C to +50 °C

Dimensions

- W x H x D: 181 x 123 x 24 mm