




Door station, 3-gang



Specification	Order No.	Packing unit	PS	EAN
 pure white	1261 66	1	18	4010337261667
 anthracite	1261 67	1	18	4010337261674
 colour aluminium	1261 65	1	18	4010337261650

Features

- Installation in a conventional flush-mounted device box.
- Fits in the cover frames of the Gira TX_44 switch range.
- Modular design, therefore easy installation and expandability with further components such as call buttons, info module, colour camera, Keyless In.
- Signal transmission and supply of the audio and video components via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- One-man start-up with easy start-up procedure.
- Weather-resistant speaker.
- High-quality electret microphone.
- Speakerphone function (voice-controlled talk-back with echo and background noise suppression).
- Call button LED lamps, white light. Even, clearly visible call-button illumination is achieved via maintenance-free, energy-saving LED technology.
- Audible acknowledgement signal when a call button is pressed.
- Adjustable voice volume.
- Sprayed-water proof call-button cover plate made of shock-resistant plastic.
- Name plate of the call button can be exchanged without tools and without frame disassembly.
- Professional labelling is available from the Gira Inscription Service www.marking.gira.com or using the Gira inscription software.
- Binary input for connecting a zero-voltage push button (NO contact) as a call button.
- Call button, 3-gang

Technical data

Power supply:	via the 2-wire bus
Bus coupler connections	
- 2-wire bus:	2x screw terminals

- Additional power supply:	2x screw terminals
- Binary input:	2x screw terminals
- Connection cable:	2 x connector strip
- Video:	1 x connector strip

Speech insert connections

- Connection cable:	2 x connector strip
---------------------	---------------------

Ambient temperature:	-25 °C to +70 °C
----------------------	------------------

Protection type:	IP44
------------------	------

Installation depth:	30 mm
---------------------	-------

Notes

- If only two call buttons are required, please use the call-button cover plate for 3-gang buttons.

Dimensions in mm

Name plates:	W 62	H 18
--------------	------	------