




Surface-mounted door station, 1 gang



| Specification | Order No. | Packing unit | PS | EAN |
|--|-----------|--------------|----|---------------|
|  pure white | 1266 66 | 1 | 18 | 4010337266662 |
|  anthracite | 1266 67 | 1 | 18 | 4010337266679 |
|  colour aluminium | 1266 65 | 1 | 18 | 4010337266655 |

Features

- Fully pre-assembled surface-mounted door station for vertical surface-mounted installation. This facilitates fast and clean installation.
- In the design of the Gira TX_44 design line.
- Torsion-resistant surface-mounted housing due to aluminium profile.
- Frame made of shatter-proof thermoplastic with high resistance to ultraviolet light as well as a scratch-resistant, care-free surface.
- Theft protection ensured by screws with hexalobular socket.
- Signal transmission and supply of the audio and video components via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- One-man commissioning with simple commissioning procedure.
- Weather-resistant loudspeaker.
- High-quality electret microphone.
- Hands-free feature (voice-controlled talk-back with echo and background noise suppression).
- Acknowledgement tone when call button is pressed.
- Voice volume adjustable.
- White call-button illumination with LED technology. Even, clearly visible call button illumination is achieved via maintenance-free, energy-saving LED technology.
- Sprayed-water proof call-button cover plate made of shock-resistant plastic.
- Name plate of the call button can be exchanged without tools and frame removal.
- Professional inscription by the Gira inscription service www.beschriftung.gira.de or the Gira inscription software.
- Low installation height of just 19 mm.

Technical data

| | |
|---------------|-------------------------------|
| Power supply: | DC 26 V ± 2 V (by 2-wire bus) |
| Connections | |
| - 2-wire bus: | 2 x screw terminal |

- Additional power supply: 2 x screw terminal

Protection class: IP44

Ambient temperature: -25 °C to +70 °C

Dimensions in mm

| | | | |
|-----------------------|-------|-------|------|
| Door station, 1-gang: | B 110 | H 181 | T 19 |
| Name plate: | B 62 | H 62 | T - |
