



Pushbutton sensor 2, 3-gang 24 V zero-voltage with inscription space



Specification	Order No.	Packing unit	PS	EAN
 clear / pure white glossy	2003 100	1	02	4010337047971
 stainless steel	2003 600	1	02	4010337020363

Features

Pushbutton sensor 2 for connection to 24 V control systems

- Three rockers with two red LEDs each for status display.
- Disassembly safeguard by screw connection.
- Backlighting.
- Connection of six buttons, six LEDs, and backlighting via the terminal block on the rear.

Technical data

Rated voltage of each button:	AC/DC 24 V SELV
Load capacity of each button:	max. 20 mA
Rated voltage of each LED:	DC 24 V SELV
Load capacity of each LED:	1 mA
Connection:	2 x 9-pole terminal block
Connections:	Ø max. 0.8 mm
Installation depth:	25 mm
Ambient temperature:	-5 °C to +45 °C

Notes

- Suitable for SELV circuits only.
 - Can also be connected with illumination.
 - Professional labelling with the Gira Inscription Service www.marking.gira.com.
-

Scope of supply

- Blank inscription labels included.
-