


## Gira Control 9 Client 2



Specification	Order No.	Packing unit	PS	EAN
	2097 00	1	05	4010337029267

The Gira Control 9 Client 2 is a display and operating unit for connection to the Gira HomeServer or Gira FacilityServer. The power-saving device is PC-based and has a TFT touch screen with LED backlighting and 22.86 cm (9") screen size (resolution of 1024 x 600 px).

### Features

- Visualisation and operation of building system technology functions in conjunction with the Gira HomeServer and/or the Gira FacilityServer or the eNet Server.
- Suitable for door communication systems as a home station (via DCS-IP gateway).
- Display of e-mails.
- Playback of acoustic signals.

#### Device features

- PC with touch screen.
- Integrated power supply unit.
- Integrated speaker.
- Integrated microphone.

### Technical data

Rated voltage: AC 110 to 230 V

#### Power consumption

- Operation: max. 20 W
- Display off: max. 8 W
- Standby: max. 1 W

#### System information

- Processor: INTEL® Atom™ E3825 Dual Core 1.33 GHz
- Mass storage: 16 GB
- RAM: 2 GB
- L2 cache: 1 MB
- Operating system: Microsoft® Windows® Embedded POSReady 7 x86 (32-bit)

#### Connections

- USB 1.1/2.0 Type A: 2 x rear, 1 x front

Illustrations are similar and may deviate from originals.

- Card slot: 1 x SDHC, to 32 GB  
- Network: 1 x RJ45, 10/100 Mbit  
- Audio: 1 x Line In, 1 x Line Out (stereo)

Display  
- Resolution: WVGA, 1024 x 600 px  
- Number of colours: 16.7 M

Ambient temperature  
- Operation: 0 °C to +40 °C  
- Storage: -10 °C to +70 °C

Relative humidity  
at +40 °C: 10 to 85 % r. H., no condensation

---

## Notes

- Can be used as a home station with the DCS-IP gateway.
- Suitable for indoor use only.

---

## Dimensions in mm

Profile height:	W 268	H 220	D 65
Profile height of the upgrade version with adapter frame :	W -	H 16	D -
	W -	H 28	D -

---