


## IP interface for KNX



| Specification                                                                         | Order No. | Packing unit | PS | EAN           |
|---------------------------------------------------------------------------------------|-----------|--------------|----|---------------|
|  DRA | 2168 00   | 1            | 26 | 4010337084457 |

## Features

- For coupling a PC to the KNX bus to address, program, or diagnose KNX components.

## Technical data

|                      |                                                                             |
|----------------------|-----------------------------------------------------------------------------|
| KNX medium:          | KNXnet/IP and TP1-256                                                       |
| Rated voltage:       | DC 24 to 30 V                                                               |
| IP communication:    | Ethernet 10/100 BaseT (10/100 Mbit/s)                                       |
| Supported protocols: | ARP, ICMP, IGMP, DHCP, AutoIP, UDP/IP (Core, Tunnelling, Device Management) |
| Connections          |                                                                             |
| - IP:                | 2 x RJ45 jacks                                                              |
| - KNX:               | Connection and junction terminal                                            |
| Ambient temperature: | 0 °C to +45 °C                                                              |

## Notes

- Power supply via external DC 24 V or via unchoked output of the Gira power supply for KNX.

## Dimensions

|                     |   |
|---------------------|---|
| Modular width (MW): | 2 |
|---------------------|---|