







EnOcean wireless wall transmitter, 1-gang



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	2421 01	1	02	4010337463825
 pure white glossy	2421 03	1	02	4010337463832
 pure white matt	2421 27	1	02	4010337463849
 anthracite	2421 28	1	02	4010337463856
 colour aluminium	2421 26	1	02	4010337463870
 black matt	2421 005	1	02	4010337037088
 grey matt	2421 015	1	02	4010337084136

Features

- Wireless transmitter for transmitting switching, dimming and blind commands to wireless receivers in the EnOcean wireless system.
- Battery-free device without external power supply. The transmission energy is generated from mechanical energy by actuating the rocker.
- Encrypted or unencrypted wireless transmission possible.

Technical data

Wireless frequency:	868.3 MHz
Range	
- in free field:	up to 300 m
- in buildings:	approx. 30 m
Ambient temperature:	-25 °C to +65 °C
Humidity:	0 to 95 % (without condensation)

Notes

- Mounting on device box or on smooth, level surfaces using screws or adhesives.
 - This product cannot be used with eNet. Gira EnOcean transmitters are compatible with third-party actuators.
-

Scope of supply

- Radio wall transmitter, comes with mounting plate, adhesive film (privacy protection for glass surfaces), and adhesive points for installation on smooth, level surfaces.
-