


Insert for network connection box Cat.6A 2-gang Insulation displacement contact technology



Specification	Order No.	Packing unit	PS	EAN
	2452 00	1	01	4010337881797

Features

- Shielded network connection box Cat.6A with two connection sockets RJ45 (8/8) for data transfer rates up to 10 Gigabit Ethernet in accordance with IEEE 802.3an.
- 45° angled socket outlet for parapet duct, floor tank and flush-mounted installation.
- Cable entry possible from all directions in 8 x 45° increments.

Technical data

Installation depth: 33 mm.

Notes

- For screw mounting only.
- Important! Observe construction space for plug and bending radii.
- If using with gender changers:
Not suitable for duct installation or a standard device box.
Connection with angled plug recommended.
- Installation recommendation:

Kaiser electronic outlets

flush-mounted installation: Kaiser Order No.: 1068-02

hollow-wall installation: Kaiser Order No.: 9062-94

concrete installation: Kaiser Order No.: 1268-40

- For screw mounting only.