


**SCHUKO socket outlet, 16 A 250 V~ with increased contact protection (Safety Plus) and USB power supply, 2-gang  
Type A / type C**

Specification	Order No.	Packing unit	PS	EAN
 pure white glossy	2459 70	1	02	4010337129967

**Features**

- Charging option for up to two end devices simultaneously using USB cable type A and type C.
- Up to two end devices can be charged simultaneously.

**Technical data**

Input voltage:	AC 220 – 250 V, 50/60 Hz
USB connection:	1 x type A, 1 x type C
Output voltage USB:	DC 5 V
Charging current	
- USB A:	max. 2.4 A
- USB C:	Max. 3 A
Standby:	≤80 mW
Connection cross section	
- for conductors from:	1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup>
Installation depth:	31 mm
Ambient temperature:	+5° C to +35° C

**Notes**

- Increased contact protection (Safety Plus) in accordance with IEC 60884-1.
- During long charging cycles, the housing of the product may heat up.
- Using a deep device box is recommended.

## Scope of supply

- Type A or type C USB cables are not included in the scope of delivery.

---