

Bluetooth® wall transmitter, 1-gang



| Specification | Order No. | Packing unit | PS | EAN |
|---|-----------|--------------|----|---------------|
|  cream white glossy | 2461 01 | 1 | 02 | 4010337110712 |
|  pure white glossy | 2461 03 | 1 | 02 | 4010337101598 |
|  pure white matt | 2461 27 | 1 | 02 | 4010337101604 |
|  anthracite | 2461 28 | 1 | 02 | 4010337101611 |
|  colour aluminium | 2461 26 | 1 | 02 | 4010337101628 |
|  black matt | 2461 005 | 1 | 02 | 4010337101635 |
|  grey matt | 2461 015 | 1 | 02 | 4010337110729 |

Features

- Wireless transmitter for transmitting switching, dimming or blind commands to the Bluetooth® wireless receivers from the System 3000 or third parties, e.g Casambi.
- Battery-free device without external power supply. The transmission energy is generated from mechanical energy by actuating the rocker.

- Configuration via the app or NFC.

Technical data

| | |
|----------------------|----------------------------------|
| Wireless frequency: | 2.402 - 2.480 GHz |
| Wireless protocol: | Bluetooth® low energy (BLE) |
| Interface: | NFC |
| Range | |
| - in free field: | up to 75 m |
| - in buildings: | approx. 10 m |
| Ambient temperature: | -25 °C to +65 °C |
| Humidity: | 0 to 95 % (without condensation) |

Notes

- Mounting on device box or on smooth, level surfaces using screws or adhesives.
 - This product cannot be used with eNet.
-

Scope of supply

- Radio wall transmitter, comes with mounting plate, adhesive film (privacy protection for glass surfaces), and adhesive points for installation on smooth, level surfaces.
-