







**Fused spur connection box, British Standard (BS 1363-4) 13 A 250 V~ switched
Support ring 71 x 71 mm**



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	2785 01	1/5	29	4010337079910
 pure white glossy	2785 03	1/5	29	4010337079927
 anthracite	2785 28	1/5	29	4010337079941
 colour aluminium	2785 26	1/5	29	4010337079934
black matt	2785 005	1/5	29	4010337037101
 grey matt	2785 015	1/5	29	4010337086994
 stainless steel (lacquered)	2785 600	1/5	29	4010337022244

Features

- With screw terminals.
- For screw mounting only.

GIRA Data sheet

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

Technical data

Installation depth: 29 mm

Connections
- maximum: 2 x 2.5 mm²
