









**British Standard Fused spur connection box (BS 1363-4) 13 A 250 V~ not switched
System 55**



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	2811 01	1/5	29	4010337035824
 pure white glossy	2811 03	1/5	29	4010337035831
 anthracite	2811 28	1/5	29	4010337035848
 colour aluminium	2811 26	1/5	29	4010337035855
 black matt	2811 005	1/5	29	4010337053354
 grey matt	2811 015	1/5	29	4010337087083
 stainless steel (lacquered)	2811 600	1/5	29	4010337035879

Features

- With screw terminals.
- For screw attachment only.

GIRA Data sheet

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

Technical data

Installation depth: 29 mm

Connection cross section
- maximum: 2 x 2.5 mm²
