

**British Standard rocker switch (BS EN 60669-1) 3-gang with rockers  
System 55, 1-way switch**



| Specification                                                                                                   | Order No. | Packing unit | PS | EAN           |
|-----------------------------------------------------------------------------------------------------------------|-----------|--------------|----|---------------|
|  cream white glossy           | 2830 01   | 10           | 29 | 4010337830016 |
|  pure white glossy           | 2830 03   | 10           | 29 | 4010337830030 |
|  anthracite                  | 2830 28   | 10           | 29 | 4010337830283 |
|  colour aluminium            | 2830 26   | 10           | 29 | 4010337830269 |
|  black matt                  | 2830 005  | 10           | 29 | 4010337038580 |
|  grey matt                   | 2830 015  | 10           | 29 | 4010337087113 |
|  Stainless steel (lacquered) | 2830 600  | 10           | 29 | 4010337022022 |

**Technical data**

|                                                     |                            |
|-----------------------------------------------------|----------------------------|
| Installation depth:                                 | 25 mm                      |
| Connection cross section<br>- for conductors up to: | 2.5 mm²                    |
| Rated output:                                       | 100 W LED load (IEC 60669) |