



British Standard rocker switch (BS EN 60669-1) 3-gang with rockers Support ring 71 x 71 mm, universal off/2-way switch



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	2832 01	10	29	4010337832010
 pure white glossy	2832 03	10	29	4010337832034
 anthracite	2832 28	10	29	4010337832287
 colour aluminium	2832 26	10	29	4010337832263
 black matt	2832 005	10	11	4010337038528
 grey matt	2832 015	10	11	4010337087120
 stainless steel (lacquered)	2832 600	10	29	4010337022053

Features

- With screw terminals.

Technical data

Installation depth:	25 mm
Connections - for conductors up to:	2.5 mm ²
Rated output:	100 W LED load (IEC 60669)

Notes

- For screw mounting only.
