








British Standard rocker switch (BS EN 60669-1) 20 AX 250 V~ with rocker and control light
Support ring 71 x 71 mm, circuit breaker, 2-pole



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	2834 01	10	29	4010337078814
 pure white glossy	2834 03	10	29	4010337078821
 anthracite	2834 28	10	29	4010337078845
 colour aluminium	2834 26	10	29	4010337078838
 black matt	2834 005	10	29	4010337038573
 grey matt	2834 015	10	29	4010337087137
 stainless steel	2834 600	10	29	4010337022305

Features

- With screw terminals.

Technical data

Installation depth:	24 mm
Connections - for conductors up to:	2 x 4 mm ² or 1 x 6 mm ²

Notes

- For screw mounting only.
