








**Pushbutton switch, 10 AX 250 V with upright rocker, 2-gang
Series switch**



Specification	Order No.	Packing unit	PS	EAN
 pure white glossy	2860 201	1/5	01	4010337065876
 pure white matt	2860 27	1/5	01	4010337029373
 anthracite	2860 28	1/5	11	4010337029397
 colour aluminium	2860 26	1/5	11	4010337029380
 black matt	2860 005	1/5	11	4010337038023
 grey matt	2860 015	1/5	11	4010337087199
 stainless steel	2860 600	1/5	11	4010337021223

Technical data

Installation depth

- 2860 ...:	28 mm
- 2861 ...:	32 mm

Connections

- for conductors up to:	2.5 mm ²
-------------------------	---------------------

Rated output

- LEDi/ CFLi:	100 W
---------------	-------

Illustrations are similar and may deviate from originals.

GIRA Data sheet

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com
