





Rocker switch 10 AX 250 V~ with rocker, 2-gang for hotel room status display



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	3104 01	1	01	4010337042495
 pure white glossy	3104 03	1	01	4010337042501
 pure white matt	3104 27	1	01	4010337042525
 anthracite	3104 28	1	11	4010337042532
 colour aluminium	3104 26	1	11	4010337042518
 black matt	3104 005	1	11	4010337069812

Features

- Switch for “Do not disturb” and “Make up room” hotel room status displays.
- With block to prevent both sides from being switched on.
- Locked both electrically and mechanically.
- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.

- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

Technical data

Installation depth: 32 mm

Connection cross section

- For rigid and flexible conductors up to: 2.5 mm²

Rated output

- LEDi/CFLi: 100 W
