




**Rocker indicator switch insert 10 AX 250 V~
with orange LED lighting element element 230 V~
circuit breaker, 2-pole**



Specification	Order No.	Packing unit	PS	EAN
 with mounting claws	3112 00	10	01	4010337038696
 without mounting claws	3822 00	1	01	4010337038702

Technical data

Installation depth

- 3112 00: 32 mm
- 3822 00: 23 mm

Connection cross section

- For rigid and flexible conductors up to: 2.5 mm²

Rated output

- LEDi/CFLi: 100 W

Notes

- Can also be connected to be illuminated by rotating the LED insert by 180°.