




Pushbutton indicator switch insert 10 AX 250 V~ circuit breaker, 2-pole, without rocker



Specification	Order No.	Packing unit	PS	EAN
 with mounting claws	3122 00	1	01	4010337038726
 without mounting claws	3842 00	1	01	4010337064381

Technical data

Installation depth

- 3122 00:	32 mm
- 3842 00:	23 mm

Connection cross section

- For rigid and flexible conductors up to:	2.5 mm ²
--	---------------------

Rated output

- LEDi/CFLi:	100 W
--------------	-------

Notes

- Can also be connected to be illuminated by rotating the LED insert by 180°.

Scope of supply

- LED lighting element 230 V~ 0.5 mA is included in the scope of supply.