




Pushbutton indicator switch insert 10 AX 250 V~ circuit breaker, 2-pole, without rocker



| Specification | Order No. | Packing unit | PS | EAN |
|--|-----------|--------------|----|---------------|
|  with mounting claws | 3122 00 | 1 | 01 | 4010337038726 |
|  without mounting claws | 3842 00 | 1 | 01 | 4010337064381 |

Technical data

Installation depth

| | |
|------------|-------|
| - 3122 00: | 32 mm |
| - 3842 00: | 23 mm |

Connection cross section

| | |
|--|---------------------|
| - For rigid and flexible conductors up to: | 2.5 mm ² |
|--|---------------------|

Rated output

| | |
|--------------|-------|
| - LEDi/CFLi: | 100 W |
|--------------|-------|

Notes

- Can also be connected to be illuminated by rotating the LED insert by 180°.

Scope of supply

- LED lighting element 230 V~ 0.5 mA is included in the scope of supply.