



Rocker button insert 10 A 250 V~ NO contac, 1-pole



| Specification | Order No. | Packing unit | PS | EAN |
|--|-----------|--------------|----|---------------|
|  with mounting claws | 3151 00 | 10/100 | 21 | 4010337038764 |
|  without mounting claws | 3871 00 | 10 | 01 | 4010337064626 |

Technical data

Installation depth

| | |
|------------|-------|
| - 3151 00: | 32 mm |
| - 3871 00: | 23 mm |

Connection cross section

| | |
|--|---------------------|
| - For rigid and flexible conductors up to: | 2.5 mm ² |
|--|---------------------|

Notes

- Can also be connected to be illuminated.