









## Rocker



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	3296 01	10	21	4010337039341
 pure white glossy	3296 03	10/100	21	4010337039358
 pure white matt	3296 27	10/100	21	4010337039372
 anthracite	3296 28	10/100	11	4010337039389
 colour aluminium	3296 26	10	11	4010337039365
 black matt	3296 005	10	11	4010337065593
 grey matt	3296 015	10	11	4010337110521
 stainless steel	3296 600	10	11	4010337043867

## Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
  - Quick mounting (3.5 turns per mounting claw).
  - Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
  - Voltage check possible from the front.
  - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
  - Rigid and flexible conductors can be used.
  - Easily accessible release lever.
  - Shatter-proof thermoplastic base.
  - LED lighting elements can be inserted from the front as standard.
  - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-