


## Upright rocker



| Specification                                                                                        | Order No. | Packing unit | PS | EAN           |
|------------------------------------------------------------------------------------------------------|-----------|--------------|----|---------------|
|  pure white glossy  | 3496 03   | 10           | 01 | 4010337121664 |
|  pure white matt  | 3496 27   | 10           | 01 | 4010337066101 |
|  anthracite       | 3496 28   | 10           | 11 | 4010337066262 |
|  colour aluminium | 3496 26   | 1            | 11 | 4010337065999 |
|  black matt       | 3496 005  | 10           | 11 | 4010337065944 |
|  grey matt        | 3496 015  | 1            | 11 | 4010337110590 |
|  stainless steel  | 3496 600  | 1/5          | 11 | 4010337066279 |

## Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.

- Voltage check possible from the front.
  - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
  - Rigid and flexible conductors can be used.
  - Easily accessible release lever.
  - Shatter-proof thermoplastic base.
  - LED lighting elements can be inserted from the front as standard.
  - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-