






Cover with control window for pull-cord switch



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	3638 01	1	01	4010337042433
 pure white glossy	3638 03	1	01	4010337042440
 pure white matt	3638 27	1	01	4010337042464
 anthracite	3638 28	1	11	4010337042471
 black matt	3638 005	1	11	4010337064350

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.