




Rocker switch insert 10 AX 250 V~ 2-way switch, 2-gang



| Specification | Order No. | Packing unit | PS | EAN |
|--|-----------|--------------|----|---------------|
|  with mounting claws | 3108 00 | 10 | 01 | 4010337038979 |
|  without mounting claws | 3818 00 | 10 | 01 | 4010337038757 |

Technical data

| | |
|--|---------------------|
| Installation depth: | 32 mm |
| Connection cross section - For rigid and flexible conductors up to: | 2.5 mm ² |
| Rated output - LEDi/CFLi: | 100 W |