




**SCHUKO socket outlet 16 A 250 V~ (IP20)
TX_44**



| Specification | Order No. | Packing unit | PS | EAN |
|--|-----------|--------------|----|---------------|
|  pure white | 4188 66 | 1/5 | 13 | 4010337093107 |
|  anthracite | 4188 67 | 1/5 | 13 | 4010337093114 |
|  colour aluminium | 4188 65 | 1/5 | 13 | 4010337093091 |

Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

| | |
|--|--|
| Installation depth: | 29 mm |
| Conductors: | Rigid and flexible |
| Connection cross section - for conductors from: | 1.5 mm ² to 2.5 mm ² |

Notes

- Not suitable for moisture-proof installation, due to protection type IP20.
 - The sealing flange of the frame must be used for installation.
-