




## SCHUKO socket outlet 16 A 250 V~ with hinged cover and inscription space TX\_44



Specification	Order No.	Packing unit	PS	EAN
 pure white	4410 66	1/5	13	4010337094166
 anthracite	4410 67	1/5	13	4010337094173
 colour aluminium	4410 65	1/5	13	4010337094159

### Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

### Technical data

Installation depth:	29 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup>

## Scope of supply

- Blank inscription label enclosed.

---

## Dimensions in mm

Height of the inscription label:	H 12
----------------------------------	------

---