









**SCHUKO socket outlet 16 A 250 V~ with hinged cover and increased contact protection (Safety Plus)  
System 55**



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	4414 01	1/5	01	4010337094388
 pure white glossy	4414 03	1/5	01	4010337094401
 pure white matt	4414 27	1/5	01	4010337094425
 anthracite	4414 28	1/5	11	4010337094432
 colour aluminium	4414 26	1/5	11	4010337094418
 black matt	4414 005	1/5	11	4010337094371
 grey matt	4414 015	1/5	11	4010337094395
 stainless steel	4414 600	1/5	11	4010337094463

## Features

- The support ring is earthed in connection with the mounting claws and claw screws.
  - Quick mounting (approx. 3.5 turns per mounting claw).
  - Expanding claws in the housing.
  - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
  - Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
  - Low installation depth.
  - Large, ergonomically shaped release levers.
  - Sturdy earth bar with solid earthing fingers.
  - Sturdy and corrosion-resistant steel support ring.
  - Shatter-proof thermoplastic base.
- 

## Technical data

Installation depth: 29 mm

### Conductors

- Rigid and flexible:

### Connection cross section

- for conductors from: 1.5 mm<sup>2</sup> to 2.5 mm<sup>2</sup>

---

## Notes

- Cover frames (1-gang to 5-gang) from the Standard 55 and Gira E2 design lines in combination with the sealing kit are also suitable for the mounting of flush-mounted SCHUKO socket outlets with hinged cover in accordance with the IP44 protection rating.
  - Increased contact protection (Safety Plus) in accordance with IEC 60884-1.
-