


**SCHUKO socket outlet 16 A 250 V~ with insert rotated by 30° and increased contact protection (Safety Plus), without mounting claws with orange cover and imprint "ZSV"(additional safety power supply)**



| Specification  | Order No. | Packing unit | PS | EAN           |
|--|-----------|--------------|----|---------------|
|  orange glossy | 4418 109  | 1/5          | 01 | 4010337094975 |

## Features

- Especially suited for angled plugs.
- Also for use in Gira energy profiles and underfloor systems.
- For screw mounting.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

## Technical data

|                                 |  |
|---------------------------------|--|
| Installation depth:             | 29 mm                                      |
| Conductors:                     | Rigid and flexible                         |
| Connection cross section        |  |
| - for conductors from:          | 1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup> |
| Ambient temperature             |  |
| - increased contact protection: | 0°C to +45°C                               |

## Notes

- Increased contact protection (Safety Plus) in accordance with IEC 60884-1.
- The bases of the SCHUKO socket outlets are colour coded accordingly.