

**SCHUKO socket outlet 16 A 250 V~ with insert rotated by 30° and increased contact protection (Safety Plus), without mounting claws  
System 55**



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	4418 01	1/5	01	4010337094920
 pure white glossy	4418 03	1/5	01	4010337094944
 pure white matt	4418 27	1/5	01	4010337094999
 anthracite	4418 28	1/5	11	4010337095026
 colour aluminium	4418 26	1/5	11	4010337094982
 black matt	4418 005	1/5	11	4010337094913
 grey matt	4418 015	1/5	11	4010337094937

## Features

- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.

- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.
- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.

---

## Technical data

Installation depth:	32 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup>
Ambient temperature - increased contact protection:	0°C to +45°C

---

## Notes

- With increased contact pressure of the grounding bar tested in compliance with T.N.O.
- Increased contact protection (Safety Plus) in accordance with IEC 60884-1.