






**Danish socket outlet 16 A 250 V~  
107-2-D1, DK 1-1b with increased contact protection (Safety Plus)  
System 55**



| Specification   | Order No. | Packing unit | PS | EAN           |
|---|-----------|--------------|----|---------------|
|  cream white glossy | 4422 01   | 1/5          | 01 | 4010337092308 |
|  pure white glossy | 4422 03   | 1/5          | 01 | 4010337092322 |
|  pure white matt   | 4422 27   | 1/5          | 01 | 4010337092346 |
|  anthracite        | 4422 28   | 1/5          | 11 | 4010337092353 |
|  colour aluminium  | 4422 26   | 1/5          | 11 | 4010337092339 |
|  black matt        | 4422 005  | 1/5          | 11 | 4010337092292 |
|  grey matt         | 4422 015  | 1/5          | 11 | 4010337092315 |

## Features

- The support ring is earthed in connection with the mounting claws and claw screws.

- Quick mounting (approx. 3.5 turns per mounting claw).
  - Expanding claws in the housing.
  - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
  - Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
  - Low installation depth.
  - Large, ergonomically shaped release levers.
  - Sturdy earth bar with solid earthing fingers.
  - Sturdy and corrosion-resistant steel support ring.
  - Shatter-proof thermoplastic base.
- 

## Technical data

|  |  |
|--|--|
| Installation depth:                                | 29 mm                                      |
| Connection cross section<br>- for conductors from: | 1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup> |

---

## Notes

- Increased contact protection (Safety Plus) in accordance with IEC 60884-1.
-