

**Danish socket outlet 16 A 250 V~**  
**107-2-D1, DK 1-1b with increased contact protection (Safety Plus)**  
**System 55**



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	4422 01	1/5	01	4010337092308
 pure white glossy	4422 03	1/5	01	4010337092322
 pure white matt	4422 27	1/5	01	4010337092346
 anthracite	4422 28	1/5	11	4010337092353
 colour aluminium	4422 26	1/5	11	4010337092339
 black matt	4422 005	1/5	11	4010337092292
 grey matt	4422 015	1/5	11	4010337092315

## Features

- The support ring is earthed in connection with the mounting claws and claw screws.

- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

---

## Technical data

Installation depth: 29 mm

Connection cross section  
- for conductors from: 1.5 mm<sup>2</sup> to 2.5 mm<sup>2</sup>

---

## Notes

- Increased contact protection (Safety Plus) in accordance with IEC 60884-1.

---