









**SCHUKO socket outlet 16 A 250 V~ with increased contact protection (Safety Plus)
Plug terminals**



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	4453 01	10/100	01	4010337093718
 pure white glossy	4453 03	10/100	01	4010337093732
 pure white matt	4453 27	10/100	01	4010337093763
 anthracite	4453 28	10/100	11	4010337093770
 colour aluminium	4453 26	10	11	4010337093756
 black matt	4453 005	10/100	11	4010337093701
 grey matt	4453 015	1/5	11	4010337093725
 stainless steel	4453 600	1/5	11	4010337093787

Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

Installation depth:	32 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm ² to 2.5 mm ²
Ambient temperature - increased contact protection:	0°C to +45°C

Notes

- Increased contact protection (Safety Plus) in accordance with IEC 60884-1.
-