








**SCHUKO socket outlet 16 A 250 V~ with imprint "EDV"
System 55**



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	4458 01	1/5	01	4010337093176
 pure white glossy	4458 03	1/5	01	4010337093190
 pure white matt	4458 27	1/5	01	4010337093213
 anthracite	4458 28	1/5	11	4010337093220
 colour aluminium	4458 26	1/5	11	4010337093206
 black matt	4458 005	1/5	11	4010337093169
 grey matt	4458 015	1/5	11	4010337093183

Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).

- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.
- Earthed support ring.

Technical data

Installation depth:	32 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm ² to 2.5 mm ²

Notes

- With increased contact pressure of the grounding bar tested in compliance with T.N.O.
-