








**SCHUKO socket outlet 16 A 250 V~ with inscription space and increased contact protection (Safety Plus)  
System 55**



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	4462 01	1/5	01	4010337093367
 pure white glossy	4462 03	1/5	01	4010337093381
 pure white matt	4462 27	1/5	01	4010337093404
 anthracite	4462 28	1/5	11	4010337093411
 colour aluminium	4462 26	1/5	11	4010337093398
 black matt	4462 005	1/5	11	4010337093350
 grey matt	4462 015	1/5	11	4010337093374

## Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).

- Expanding claws in the housing.
  - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
  - Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
  - Low installation depth.
  - Large, ergonomically shaped release levers.
  - Sturdy earth bar with solid earthing fingers.
  - Sturdy and corrosion-resistant steel support ring.
  - Shatter-proof thermoplastic base.
- 

## Technical data

Installation depth:	29 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup>
Ambient temperature - increased contact protection:	0°C to +45°C

---

## Notes

- Increased contact protection (Safety Plus) in accordance with IEC 60884-1.
- 

## Scope of supply

- Inscription label "EDV" is enclosed.
-