









**Socket outlet with earth pin 16 A 250 V~
and increased contact protection (Safety Plus)
System 55**



| Specification | Order No. | Packing unit | PS | EAN |
|---|-----------|--------------|----|---------------|
|  cream white glossy | 4485 01 | 1/5 | 01 | 4010337095668 |
|  pure white glossy | 4485 03 | 10/100 | 01 | 4010337095682 |
|  pure white matt | 4485 27 | 10 | 01 | 4010337095712 |
|  anthracite | 4485 28 | 10 | 11 | 4010337095729 |
|  colour aluminium | 4485 26 | 10 | 11 | 4010337095705 |
|  black matt | 4485 005 | 10 | 11 | 4010337095651 |
|  grey matt | 4485 015 | 1/5 | 11 | 4010337095675 |
|  stainless steel | 4485 600 | 1/5 | 11 | 4010337095736 |

Features

- With plug terminals.
 - The support ring is earthed in connection with the mounting claws and claw screws.
 - Quick mounting (approx. 3.5 turns per mounting claw).
 - Expanding claws in the housing.
 - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
 - Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
 - Low installation depth.
 - Large, ergonomically shaped release levers.
 - Sturdy earth bar with solid earthing fingers.
 - Sturdy and corrosion-resistant steel support ring.
 - Shatter-proof thermoplastic base.
-

Technical data

| | |
|-------------------------------------|--|
| Installation depth: | 29 mm |
| Replaces fully compatible 0485 ...: | |
| Connection cross section | |
| - for conductors from: | 1.5 mm ² to 2.5 mm ² |
| Ambient temperature | |
| - increased contact protection: | 0°C to +45°C |

Notes

- Approved in accordance with NF C 61-314:2017.
 - Approved in accordance with NBN C 61-112-1:2017.
 - Increased contact protection (Safety Plus) in accordance with IEC 60884-1.
-