



## Socket outlet with earth pin 16 A 250 V~and shutter



Specification	Order No.	Packing unit	PS	EAN
 pure white glossy	4485 112	1/5	01	4010337103998

### Features

- With plug terminals.
- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

### Technical data

Installation depth:	29 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup>
Ambient temperature - shutter:	0°C to +45°C

### Notes

- Approved in accordance with NF C 61-314 (2003).
- Increased contact protection (Safety Plus) in accordance with IEC 60884-1.