









**Socket outlet with earth pin 16 A 250 V~,
hinged cover and protección ampliada contra contacto accidental (Safety Plus)
System 55**



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	4488 01	10	01	4010337095804
 pure white glossy	4488 03	10	01	4010337095835
 pure white matt	4488 27	10	01	4010337095859
 anthracite	4488 28	10	11	4010337095866
 colour aluminium	4488 26	10	11	4010337095842
 black matt	4488 005	10	11	4010337095798
 grey matt	4488 015	10	11	4010337095811
 stainless steel	4488 600	1/5	11	4010337095873

Features

- With plug terminals.
- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

Installation depth:	29 mm
Conductors:	Rigid and flexible
Connection cross section	
- for conductors from:	1.5 mm ² to 2.5 mm ²
Ambient temperature	
- increased contact protection:	0°C to +45°C

Notes

- Approved in accordance with NF C 61-314:2017.
 - Approved in accordance with NBN C 61-112-1:2017.
 - Increased contact protection (Safety Plus) in accordance with IEC 60884-1.
-