








**SCHUKO socket outlet 16 A 250 V~ with hinged cover, control light and shutter
System 55**



| Specification | Order No. | Packing unit | PS | EAN |
|---|-----------|--------------|----|---------------|
|  cream white glossy | 4552 01 | 1/5 | 01 | 4010337095200 |
|  pure white glossy | 4552 03 | 1/5 | 01 | 4010337095217 |
|  pure white matt | 4552 27 | 1/5 | 01 | 4010337095231 |
|  anthracite | 4552 28 | 1/5 | 11 | 4010337095248 |
|  colour aluminium | 4552 26 | 1/5 | 11 | 4010337095224 |
|  black matt | 4552 005 | 1/5 | 11 | 4010337095194 |
|  grey matt | 4552 015 | 1/5 | 11 | 4010337095255 |

Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).

- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

| | |
|--|--|
| Installation depth: | 29 mm |
| Conductors: | Rigid and flexible |
| Connection cross section - for conductors from: | 1.5 mm ² to 2.5 mm ² |
| Ambient temperature - shutter: | 0°C to +45°C |

Notes

- Increased contact protection (Safety Plus) in accordance with IEC 60884-1.

Scope of supply

- A neon lamp element is included in the scope of supply.
-