







**SCHUKO socket outlet 16 A 250 V~ with hinged cover, control light and increased contact protection (Safety Plus)
System 55**



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	4552 01	1/5	01	4010337095200
 pure white glossy	4552 03	1/5	01	4010337095217
 pure white matt	4552 27	1/5	01	4010337095231
 anthracite	4552 28	1/5	11	4010337095248
 colour aluminium	4552 26	1/5	11	4010337095224
 black matt	4552 005	1/5	11	4010337095194
 grey matt	4552 015	1/5	11	4010337095255

Features

- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).

- Expanding claws in the housing.
 - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
 - Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
 - Low installation depth.
 - Large, ergonomically shaped release levers.
 - Sturdy earth bar with solid earthing fingers.
 - Sturdy and corrosion-resistant steel support ring.
 - Shatter-proof thermoplastic base.
-

Technical data

Installation depth:	29 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm ² to 2.5 mm ²
Ambient temperature - increased contact protection:	0°C to +45°C

Notes

- Increased contact protection (Safety Plus) in accordance with IEC 60884-1.
-

Scope of supply

- A neon lamp element is included in the scope of supply.
-