


SCHUKO socket outlet 16 A 250 V~ with increased contact protection (Safety Plus), without mounting claws

Specification	Order No.	Packing unit	PS	EAN
 pure white glossy	4755 70	1/5	01	4010337117513

Features

- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

Technical data

Installation depth:	32 mm
Conductors:	Rigid and flexible
Connection cross section - for conductors from:	1.5 mm ² to 2.5 mm ²
Ambient temperature - increased contact protection:	0°C to +45°C

Notes

- With increased contact pressure of the grounding bar tested in compliance with T.N.O.
- Increased contact protection (Safety Plus) in accordance with DIN VDE 0620-1.
- Increased contact protection (Safety Plus) in accordance with IEC 60884-1.