

eNet Radio remote control, 2-gang



Specification	Order No.	Packing unit	PS	EAN
 anthracite	5352 10	1	42	4010337774082

Features

- The eNet wireless transmitters send switching, dimming and blind motion commands to corresponding eNet wireless receivers.
- Two buttons belong to each channel.
- Each pair of buttons can be set as channel or scene function.
- Status LED.
- Battery-operated device.

Can be set with eNet server:

- Fully encrypted wireless transmission (AES CCM) from eNet Server software version 2.0.
- Signalling of the transmission status can be switched off.
- Operation locks.
- All-On or All-Off scenes, threshold value scenes, and individual scenes can be configured.
- Configuration of scene button using eNet SMART HOME App (if-then rules) to trigger actions, scenes and timers.
- Device software update.

Technical data

Ambient temperature: -5 °C to +45 °C

Wireless frequency: 868.3 MHz

Range (free field): approx. 100 m

Rated voltage: DC 3 V

Battery

- Type: CR 2450N
- UN no.: 3091

Dimensions

- W x H x D: 40,5 x 55 x 15 mm

Notes

- Batteries are consumables and must be replaced regularly. Please observe the regulations on the disposal of used batteries.
 - Radio approval is valid for EU and EFTA countries.
-

Scope of supply

- Batteries are included with delivery.
-