









## System 3000 touch top unit



| Specification   | Order No. | Packing unit | PS | EAN           |
|---|-----------|--------------|----|---------------|
|  cream white glossy  | 5365 01   | 1/5          | 02 | 4010337096856 |
|  pure white glossy | 5365 03   | 1/5          | 02 | 4010337096863 |
|  pure white matt   | 5365 27   | 1/5          | 02 | 4010337096887 |
|  anthracite        | 5365 28   | 1/5          | 02 | 4010337096894 |
|  colour aluminium  | 5365 26   | 1/5          | 02 | 4010337096870 |
|  black matt        | 5365 005  | 1/5          | 02 | 4010337096917 |
|  grey matt         | 5365 015  | 1/5          | 02 | 4010337107071 |
|  stainless steel   | 5365 600  | 1/5          | 02 | 4010337096900 |

## Features

- Operated by gently touching or swiping the operating surface.
  - Three brightness values can be stored, with System 3000 dimming insert.
  - The runtime and an individual intermediate position can be saved using the System 3000 blind controller insert.
  - Blocking function, with System 3000 blind control insert.
  - Status display using LED light bars to indicate the brightness or hanging position.
  - Permanent or temporary status display (status display goes out after 5 seconds if not touched).
  - Operation on System 3000 switching, dimming or blind insert and 3-wire auxiliary unit.
- 

## Technical data

Ambient temperature: -5°C to +45°C

---