









System 3000 room temperature controller Display



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	5393 01	1/5	02	4010337055112
 pure white glossy	5393 03	1/5	02	4010337055129
 pure white matt	5393 27	1/5	02	4010337055174
 colour aluminium	5393 26	1/5	02	4010337055167
 anthracite	5393 28	1/5	02	4010337055181
 black matt	5393 005	1/5	02	4010337055235
 grey matt	5393 015	1/5	02	4010337087311
 stainless steel	5393 600	1/5	02	4010337055211

Features

- Operation via capacitive sensor surface.
- Manual and time-controlled room temperature regulation.
- The current time can be stored as a switching time, quick programming.
- Automatic summer/winter time switchover, deactivatable.
- Timer with three memory areas. For each memory area comfort and lowering time for Mon-Fri and Sat+Sun.
- Setting of a comfort, reduction, cooling and frost protection temperature.
- Controller output: Pulse width modulation (PWM) or 2-point control.
- Heating optimisation (the temperature is reached at the set time).
- Adaptation to valves (normally open or normally closed).
- Activation of cooling mode via the insert.
- Supports internal and external temperature sensors.
- Temperature drop detection.
- Operation lock.
- Valve protection function.
- The display switches off after 2 minutes, permanent display of the current time is possible.
- The combination of the top unit 5394xx with 540700 is only possible for I05 (index) or higher.

Technical data

Accuracy per month:	± 10 s
Power reserve:	approx. 4 h
Ambient temperature:	-5 °C to +45 °C
