


eNet wireless receiver module



Specification	Order No.	Packing unit	PS	EAN
 DRA	5452 00	1	42	4010337774303

Features

- The eNet wireless reception module is a radio receiver for max. 32 eNet wireless DIN-rail mounting modules.
- Operation with power supply.
- Integrated antenna.
- External antenna can be connected additionally in unfavourable installation conditions.

Technical data

Rated voltage:	DC 12 V SELV
Current consumption:	15 mA
Ambient temperature:	-5 °C to +45 °C
Wireless frequency:	868.0 to 868.6 MHz
Range (free field):	approx. 100 m
Data cable:	J-Y(St)Y 2x2x0.8
Length of the data cable:	max. 3 m
Number of eNet DRA modules:	max. 32

Notes

- Wireless approval is valid for EU and EFTA countries.
- Installation in a distribution box or sub-distribution with a metal housing requires an additional antenna. The additional antenna is to be placed outside the metal housing.

Dimensions

Modular widths (MW): 2
