


## DCS-IP data interface



Specification	Order No.	Packing unit	PS	EAN
	5500 000	1	10	4010337052685

## Features

- The data interface is used to expand the current push-button start-up procedure by adding convenient start-up via PC/laptop and to connect the 2-wire bus to IP.
- Configuration via Gira Project Assistant (GPA).
- Start-up of large projects.
- Reading out of the configuration data of existing systems.
- Connection of Gira 2-wire bus to IP.
- Only suitable for indoor use.

## Technical data

### Power supply

- 2-wire bus: DC 24 V  $\pm$ 2 V
- Additional power supply: DC 12 V to 26 V
- Current consumption: max. 5 mA

### Connections

- 2-wire bus: 2 x plug terminal
- Additional power supply: 2 x plug terminal

### Optical display

- Mode: orange
- Fct./Prog.: green

### IP communication:

Ethernet 10/100 BaseT (10/100 Mbit/s)

### Ambient temperature:

-5 °C to +45 °C

### Humidity:

93% rel. humidity

### Protection class:

III (as per IEC 61140)

## Dimensions

Modular width (MW): 2

---