




DVI (24+5) insert Gender changer



| Specification | Order No. | Packing unit | PS | EAN |
|---|-----------|--------------|----|---------------|
|  cream white glossy | 5644 01 | 1/5 | 01 | 4010337460725 |
|  pure white glossy | 5644 03 | 1/5 | 01 | 4010337460732 |
|  black matt | 5644 10 | 1 | 01 | 4010337460749 |

Technical data

Installation depth
- Gender changer: at least 12 mm

Notes

- For screw mounting only.
- Important! Observe construction space for plug and bending radii.
- If using with gender changers:
Not suitable for duct installation or a standard device box.
Connection with angled plug recommended.
-
-