






**Rocker switch 10 AX 250 V~with rocker, 2-gang  
Series switch**



Specification	Order No.	Packing unit	PS	EAN
 pure white glossy	0105 03	1	01	4010337105039
 pure white matt	0105 27	1/5	01	4010337105275
 anthracite	0105 28	1	11	4010337105282
 colour aluminium	0105 26	1	11	4010337105268
black matt	0105 005	1	11	4010337038603
 stainless steel	0105 600	1	11	4010337028390

**Technical data**

Installation depth:	28 mm
Connection cross section - For rigid and flexible conductors up to:	2.5 mm <sup>2</sup>
Rated output - LEDi/CFLi:	100 W