








**Pushbutton switch 10 AX 250 V~with upright rocker
Intermediate switch**



Specification	Order No.	Packing unit	PS	EAN
 pure white glossy	0123 201	1/5	01	4010337052708
 pure white matt	0123 27	1/5	01	4010337029342
 anthracite	0123 28	1/5	11	4010337029366
 colour aluminium	0123 26	1	11	4010337029359
 black matt	0123 005	1	11	4010337037996
 grey matt	0123 015	1	11	4010337077114
 stainless steel	0123 600	1	11	4010337021254

Technical data

Installation depth:	28 mm
Connection cross section - For rigid and flexible conductors up to:	2.5 mm ²
Rated output - LEDi/CFLi:	100 W

GIRA Data sheet

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com
